

34mm Max. Aperture, Iris Diaphragm



Stock #41-972 In Stock

⊖ 1 ⊕ **€98,00**

ADD TO CART

Qty 1-4

€98,00

Qty 5+

€86,40

Volume Pricing

[Request Quote](#)

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Type:
Unmounted

Minimum Aperture (mm):
1.5

Maximum Aperture (mm):
34.0

Outer Diameter (mm):
49.0

Construction:
Brass Housing, Blue Tempered Steel Leaves

Lever Diameter (mm):
3.00

Lever Length (mm):
12.00

Number of Leaves:
14.00

Thickness (mm):
6.50

Regulatory Compliance

RoHS 2015:
[Exempt](#)

Certificate of Conformance:
[View](#)

REACH 241:
[Contains SVHC\(s\)](#)
