

4X 65mm WD, In-Line Illumination Telecentric Lens



Stock #62-793 3-4 DAYS

- 1 + **€1.190,00**

ADD TO CART

Qty 1+
€1.190,00

Volume Pricing
Request Quote

Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Length (mm): 110.00
Ferrule Diameter (inches): 0.312
Horizontal Field of View, 1/2" Sensor: 1.6mm
Horizontal Field of View, 2/3" Sensor: 2.2mm
Maximum Diameter (mm): 17.0

Horizontal Field of View @ Max Sensor Format: 2.2mm
Type: Telecentric Lens
Primary Magnification PMAG: 4X
Maximum Sensor Format: 2/3"
Working Distance (mm): 65.00
Mount: C-Mount
Style: In-Line Illumination
Aperture (f#): f/26.2
Distortion (%): ≤0.1
Compatible Light Guide/Source: 1/4" (0.312")
Lens Wavelength Range: VIS

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View