

5 LED, White Adjustable LED Bar Light



Stock **#34-875** 3-4 DAYS

⊖ 1 ⊕

€570,00

ADD TO CART

Qty 1+

€570,00

Volume Pricing

[Request Quote](#)

⚠ Prices shown are exclusive of VAT/local taxes

Note: This item requires accessories for use | [Learn More](#)

Get Product Downloads

Color:
White

Connector:
M12, 5 pins

Input Voltage (V):
24VDC

Model Number: EFFI-FLEX-5-000
Mount: 2 Rails (1 for M6 T-Nuts)
Operating Temperature (°C): -10 to 50
Dimensions (mm): 135.0 x 51.0 x 49.0
Power Supply: Power Supply Required and Sold Separately. USA: #15-874 Europe: #15-875 Japan: #15-874 Korea: #15-874 China: #15-874
Number of LEDs: 5.00
Type of Illumination: LED Illuminator
Geometry: Line Light
Illumination Mode: Strobed or Constant
Environmental Rating: IP40

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View