


In order to provide more accurate inventory information, please select your shipping country.

Select Your Country/Region: European Union



SUBMIT

TECHSPEC® 50 X 50mm Protected Gold, 4-6λ Mirror



Stock #43-887 3-4 DAYS

- 1 + €83,00

ADD TO CART

Qty 1-5
€83,00
Qty 6+
€63,50
Volume Pricing
Request Quote

Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Surface Flatness (P-V):
4 - 6λ

Substrate: ☐
Float Glass

Surface Quality:
60-40

Dimensions (mm):

50.0 x 50.0
Dimensional Tolerance (mm): ±0.25
Coating Specification: R _{avg} >96% @ 700 - 2000nm R _{avg} >96% @ 2000 - 10,000nm
Coating: Protected Gold (700-10000nm)
Coating Type: Metal
Clear Aperture CA (mm): 47.50 x 47.50
Edges: Seamed, 0.5mm Maximum Edge Chip
Thickness (mm): 3.00
Type: Flat Mirror
Wavelength Range (nm): 700 - 10000
Length (mm): 50.00
Width (mm): 50.00
Damage Threshold, By Design: ☐ 0.8 J/cm² @ 1064nm, 10ns

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant
