

In order to provide more accurate inventory information, please select your shipping country.

Select Your Country/Region: European Union

SUBMIT

TECHSPEC® 50.0mm Dia. X -125 FL, Uncoated, Plano-Concave Lens



TECHSPEC Uncoated Plano-Concave (PCV) Lenses



Stock #45-038 3-4 DAYS

[Other Coating Options](#)

1 €47,50

ADD TO CART

Qty 1-9

€47,50

Qty 10+

€42,75

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Diameter (mm):
50.00 +0.0/-0.025

Effective Focal Length EFL (mm): -125.00
Substrate: N-BK7
f/#: 2.5
Numerical Aperture NA: 0.20
Coating: Uncoated
Type: Plano-Concave Lens
Wavelength Range (nm): 350 - 2200
Back Focal Length BFL (mm): -128.30
Bevel: Protective bevel as needed
Center Thickness CT (mm): 5.00
Center Thickness Tolerance (mm): ±0.10
Centering (arcmin): <1
Clear Aperture CA (mm): 49.00
Edge Thickness ET (mm): 9.87
Focal Length Specification Wavelength (nm): 587.6
Focal Length Tolerance (%): ±1
Radius R₁ (mm): -64.60
Surface Quality: 40-20
Power (P-V) @ 632.8nm: 1.5λ
Irregularity (P-V) @ 632.8nm: λ/4

Regulatory Compliance

RoHS 2015: Compliant
Reach 219: Compliant
Certificate of Conformance: View