

TECHSPEC® 50.0/50.8mm Optic Dia., Kinematic Mount, 3-Screws



50/50.8mm Diameter Kinematic Mount, 3-Screws , #58-855

Stock **#58-855** 3-4 DAYS

⊖ 1 ⊕ **€145,00**

ADD TO CART

Qty 1-4

€145,00

Qty 5+

€130,50

Volume Pricing

[Request Quote](#)

⚠ Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Type:
Adjustable - Tip-Tilt

Type of Optics:
Circular

Size of Compatible Optics (mm):
50.0 - 50.8

Number of Adjustment Screws: 3
Clear Aperture CA (mm): 45.9
Travel (mm): Z-Axis: 12
Construction: Aluminum Plates, Stainless Steel Screws, and Brass Thread Bushings
Angle Tolerance (°): 0.2 per 0.25mm turn
Fine Tilt Angle (°): ±5
Fine Tip Angle (°): ±5
Sensitivity per 1° Knob Rotation (arcsec): 2.3
Thermal Stability (μrad): <5
Adjustment Screw Pitch (mm): 0.25
Note: Available in Quick Start Kit: #17-524
Compatible Post: M4 x0.7, 8-32
Min. Thickness of Compatible Optics (mm): 2.0
Pointing Stability (μrad): 1.3

Regulatory Compliance

RoHS 2015: Compliant
Reach 224: Compliant
Certificate of Conformance: View