

TECHSPEC® 50.8mm Dia. x 50.0mm EFL, Uncoated, Concave Laser Mirror



TECHSPEC Uncoated Concave Mirrors

Stock **#11-347** 3-4 DAYS

⊖ 1 ⊕ **€200,00**

ADD TO CART

Qty 1-4

€200,00

Qty 5+

€176,00

Volume Pricing

[Request Quote](#)

⚠ Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Substrate: ☐
[Fused Silica](#) (Coming 7980)

Surface Quality:
20-10

Diameter (mm):
50.80 +0.00/-0.20

Effective Focal Length EFL (mm): 50.00
Radius of Curvature (mm): 100.00
Coating: Uncoated
Back Surface: Fine Grind
Center Thickness CT (mm): 6.72
Clear Aperture (%): 90
Edge Thickness ET (mm): 10.00 ±0.20
Radius R₁ (mm): 100.00
Type: Concave Mirror
Irregularity (P-V) @ 632.8nm: 3λ/20

Regulatory Compliance

RoHS 2015: Compliant
Reach 219: Compliant
Certificate of Conformance: View
