

In order to provide more accurate inventory information, please select your shipping country:

Select Your Country/Region: European Union

SUBMIT

TECHSPEC® 50.8mm Dia. X 101.6mm EFL, Protected Gold 50A 90° Off-Axis Mirror



TECHSPEC Gold Off-Axis Parabolic Mirrors

Stock #37-309 3-4 DAYS

[Other Coating Options](#)



1



€510,00

ADD TO CART

Qty 1-5

€510,00

Qty 6+

€459,00

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Type:
Off-Axis Parabolic Mirror

Diameter (mm):
50.80 +0.0/-0.1

Effective Focal Length EFL (mm): 101.60
Focal Length Tolerance (%): ±1
Radius of Curvature (mm): 101.60
Coating: Protected Gold (700-10000nm)
Coating Type: Metal
Coating Specification: R _{avg} ≥94% @ 700 - 800nm R _{avg} ≥97% @ 800 - 2,000nm R _{avg} ≥98% @ 2,000 - 12,000nm
Off-Set Angle (°): 90
Parent Focal Length PFL (mm): 50.8
Surface Figure, RMS: λ/8
Surface Roughness (Angstroms): <50 RMS
Wavelength Range (nm): 700 - 10000
Surface Quality: 80-50
Compatible Mounting Plates: #47-112
Substrate: Aluminum 6061-T6
Y Offset (mm): 101.60
Reflected Wavefront, RMS: λ/4

Regulatory Compliance

RoHS 2015: Compliant
Reach 209: Compliant
Certificate of Conformance: View
