


TECHSPEC® 50mm Dia., 1mm Thick, Uncoated, B270 Window

See More by [SCHOTT Optical Components](#)



Stock #17-168 3-4 DAYS

⊖ 1 ⊕ **€58,00**

ADD TO CART

Qty 1-5
€58,00

Qty 6+
€46,50

Volume Pricing
Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Abbe Number (v_d):
58.3

Bevel:
Protective as needed

Clear Aperture CA (mm):
45.00

Diameter (mm): 50.00 +0.00/-0.25
Thickness (mm): 1.00 ±0.10
Coating: Uncoated
Coefficient of Thermal Expansion CTE (10⁻⁶/°C): 9.4 (+20 to +300°C)
Density (g/cm³): 2.56
Edges: Fine Ground
Index of Refraction n_d: 1.523
Knoop Hardness (kg/mm²): 500
Poisson's Ratio: 0.22
Substrate: B270
Surface Flatness (P-V): 1λ (per 25.4mm Dia. within CA)
Surface Quality: 60-40
Type: Protective Window
Wavelength Range (nm): 360 - 2700
Young's Modulus (GPa): 71.5

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 240: Compliant