

In order to provide more accurate inventory information, please select your shipping country.

Select Your Country/Region: European Union

SUBMIT

TECHSPEC® 50mm Dia. Protected Silver Coated, N/10 ZERODUR® Mirror



Stock #39-916 ☐ In Stock

- 1 + €222,00

ADD TO CART

Qty 1-5

€222,00

Qty 6+

€177,50

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Diameter (mm):
50.00 +0.00/-0.20

Surface Flatness (P-V):
λ/10 (measured before coating)

Substrate: ☐
ZERODUR®

Back Surface: Commercial Polish
Surface Quality: 20-10
Coating Specification: R _{avg} >98% @ 450 - 2000nm R _{avg} >98% @ 2000 - 10,000nm
Coating: Protected Silver (450-10000nm)
Coating Type: Metal
Bevel: Protective bevel as needed
Clear Aperture (%): 90
Edges: Ground
Parallelism (arcsec): 30
Thickness (mm): 5.00 ±0.20
Type: Flat Mirror
Wavelength Range (nm): 450 - 10000
Coefficient of Thermal Expansion CTE (10⁻⁶/°C): 0.1
Damage Threshold, Reference: ☐ 0.5 J/cm² @ 532nm & 1064nm, 10ns

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 233: Compliant