

TECHSPEC® 50mm Dia Enhanced Aluminum, 4-6λ Mirror



Stock **#45-614** 3-4 DAYS

- 1 + **€38,50**

ADD TO CART

Qty 1-5
€38,50

Qty 6+
€30,50

Volume Pricing
Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Diameter (mm):
50.00 ±0.25

Surface Flatness (P-V):
4 - 6λ

Substrate: ☐
Float Glass

Surface Quality:

60-40
Dimensional Tolerance (mm): ±0.25
Coating Specification: R _{avg} ≥95% @ 450 - 650nm @ 45°
Coating: Enhanced Aluminum (450-650nm)
Coating Type: Metal
Clear Aperture CA (mm): 47.50
Edges: Ground, 0.5mm Maximum Edge Chip
Thickness (mm): 3.00 nominal
Type: Flat Mirror
Wavelength Range (nm): 450 - 650
Damage Threshold, By Design: ☐ 0.2 J/cm² @ 532nm, 10ns

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 233: Compliant