


In order to provide more accurate inventory information, please select your shipping country.

Select Your Country/Region: European Union



SUBMIT



TECHSPEC® Fused Silica Wedged Windows

Stock #34-243 3-4 DAYS



1



€230,00

ADD TO CART

Qty 1-5

€230,00

Qty 6+

€184,00

Volume Pricing

[Request Quote](#)

⚠ Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Clear Aperture CA (mm):
45.00

Diameter (mm):
50.00 +0.0/-0.10

Thickness (mm):
3.00 ±0.20

Coating: Uncoated
Coefficient of Thermal Expansion CTE (10⁻⁶/°C): 0.52 (+5 to +35°C) 0.57 (0 to +200°C) 0.48 (-100 to +200°C)
Edges: Fine Ground
Index of Refraction n_d: 1.458
Substrate: ☐ Fused Silica (Corning 7980)
Surface Flatness (P-V): λ/10
Surface Quality: 20-10
Type: Wedged Window
Wavelength Range (nm): 200 - 2200
Young's Modulus (GPa): 73
Wedge Angle: 30' ±10'

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 240: Compliant