

TECHSPEC® 50mm Dia. x 150mm FL Uncoated Calcium Fluoride PCX Lens



TECHSPEC Calcium Fluoride Plano-Convex (PCX) Lenses

Stock **#88-169** 3-4 DAYS



1



€465,00

ADD TO CART

Qty 1-5

€465,00

Qty 6+

€372,00

Volume Pricing

[Request Quote](#)

⚠ Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Diameter (mm):
50.00 +0.00/-0.10

Effective Focal Length EFL (mm):
150.00 @ 266nm

Back Focal Length BFL (mm):

145.21
Coating: Uncoated
Substrate: ☐ Calcium Fluoride (CaF ₂)
Surface Quality: 40-20
Power (P-V) @ 632.8nm: λ
Irregularity (P-V) @ 632.8nm: 3λ/2
Centering (arcmin): <3
Center Thickness CT (mm): 7.00 ±0.1
Edge Thickness ET (mm): 2.33
Radius R₁ (mm): 69.31
Clear Aperture CA (mm): 45
f#: 3.00
Numerical Aperture NA: 0.17
Type: Plano-Convex Lens
Bevel: Protective bevel as needed
Wavelength Range (nm): 200 - 7000
Axis Orientation: Random

Regulatory Compliance

RoHS 2015: Compliant
Reach 219: Compliant
Certificate of Conformance: View