

TECHSPEC® 50mm Dia. x 50mm FL, 3 - 5µm Coated, Ge Plano-Convex Lens



Stock **#69-658** 3-4 DAYS

[Other Coating Options](#)



1



€950,00

ADD TO CART

Qty 1-5

€950,00

Qty 6+

€760,00

Volume Pricing

[Request Quote](#)

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Diameter (mm):
50.00 +0.0/-0.1

Effective Focal Length EFL (mm):
50.00 @ 10.6µm

Back Focal Length BFL (mm):

48.76
Coating: BBAR (3000-5000nm)
Coating Specification: R _{avg} <3.0% @ 3 - 5µm
Substrate: □ Germanium (Ge)
Surface Quality: 60-40
Centering (arcmin): <3
Center Thickness CT (mm): 5.00 ±0.10
Edge Thickness ET (mm): 2.90
Radius R₁ (mm): 150.21
Clear Aperture CA (mm): 49
f#: 1.00
Numerical Aperture NA: 0.50
Type: Plano-Convex Lens
Bevel: Protective bevel as needed
Wavelength Range (nm): 3000 - 5000

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant