

In order to provide more accurate inventory information, please select your shipping country:

Select Your Country/Region: European Union

SUBMIT

TECHSPEC® 5.0mm Dia. X 5.0mm FL, Uncoated, Plano-Convex Lens



Stock #45-227 ☐ In Stock
[Other Coating Options](#)

1 €35,50

ADD TO CART

Qty 1-9
€35,50
Qty 10+
€32,00
Volume Pricing
Request Quote

Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Diameter (mm):
5.00 +0.0/-0.025

Effective Focal Length EFL (mm):

5.00 @ 587.6nm
Back Focal Length BFL (mm): 3.96
Coating: Uncoated
Substrate: ☐ N-LASF44
Surface Quality: 40-20
Power (P-V) @ 632.8nm: 1.5λ
Irregularity (P-V) @ 632.8nm: λ/4
Focal Length Tolerance (%): ±1
Centering (arcmin): 30-45, typical
Center Thickness CT (mm): 1.87 ±0.05
Edge Thickness ET (mm): 1.00
Radius R ₁ (mm): 4.02
Clear Aperture CA (mm): 4.5
f/#: 1
Numerical Aperture NA: 0.50
Type: Plano-Convex Lens
Bevel: Protective bevel as needed
Wavelength Range (nm): 350 - 2300

Regulatory Compliance

RoHS 2015: Compliant
Reach 219: Compliant
Certificate of Conformance: View