



50mm H x 25mm L x 100mm FL VIS 0° Coated, Illumination Grade PCX Cylinder Lens



Stock **#69-737** 3-4 DAYS

- 1 + **€129,00**

ADD TO CART

Qty 1-5
€129,00

Qty 6+
€103,00

Volume Pricing
Request Quote

Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Effective Focal Length EFL (mm):
100.00

Substrate: ☐
[N-BK7](#)

f#:

2
Numerical Aperture NA: 0.25
Coating: VIS 0° (425-675nm)
Type: Cylinder Lens, Plano-Convex
Wavelength Range (nm): 425 - 675
Back Focal Length BFL (mm): 94.93
Center Thickness CT (mm): 7.70
Center Thickness Tolerance (mm): ±0.1
Coating Specification: R _{avg} ≤0.4% @ 425 - 675nm
Dimensional Tolerance (mm): +0.0/-0.2
Dimensions (mm): 50.0 x 25.0
Edge Thickness ET (mm): 1.28
Focal Length Tolerance (%): ±3
Radius R₁ (mm): 51.85
Surface Quality: 60-40
Damage Threshold, Reference:  5 J/cm ² @ 532nm, 10ns

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant