

TECHSPEC® 50mm H x 25mm L x 75mm FL Uncoated, Illumination Grade PCX Cylinder Lens



Stock **#46-198** ☐ In Stock

-

1

+

€110,00

ADD TO CART

Qty 1-5
€110,00
Qty 6+
€88,00
Volume Pricing
Request Quote

Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Effective Focal Length EFL (mm):
75.00

Substrate: ☐
[N-BK7](#)

f/#:
1.5

Numerical Aperture NA: 0.33
Coating: Uncoated
Type: Cylinder Lens, Plano-Convex
Wavelength Range (nm): 350 - 2200
Back Focal Length BFL (mm): 68.07
Center Thickness CT (mm): 10.53
Center Thickness Tolerance (mm): ±0.1
Dimensional Tolerance (mm): +0.0/-0.2
Dimensions (mm): 50.0 x 25.0
Edge Thickness ET (mm): 1.43
Focal Length Tolerance (%): ±3
Radius R₁ (mm): 38.89
Surface Quality: 60-40

Regulatory Compliance

RoHS 2015: Compliant
Reach 224: Compliant
Certificate of Conformance: View