

In order to provide more accurate inventory information, please select your shipping country.

Select Your Country/Region: European Union



SUBMIT

36mm Max. Aperture, Stainless Steel Iris Diapnragm



Stock #64-505 3-4 DAYS

- 1 + €96,00

ADD TO CART

Qty 1-4
€96,00
Qty 5+
€85,10
Volume Pricing
Request Quote

Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Type:
Unmounted

Minimum Aperture (mm):
1.9

Maximum Aperture (mm):
36.0

Outer Diameter (mm):

50.0
Construction: Blackened Aluminum Housing, Stainless Steel Leaves
Lever Diameter (mm): 3.00
Lever Length (mm): 12.50
Number of Leaves: 16.00
Thickness (mm): 6.00

Regulatory Compliance

RoHS 2015: Exempt
Certificate of Conformance: View
Reach 240: Contains SVHC(s)