


TECHSPEC® 50mm Square 45°, Red Dichroic Filter



Stock **#47-948** 3-4 DAYS

⊖ 1 ⊕ **€138,00**

ADD TO CART

Qty 1-10
€138,00
Qty 11+
€117,30
Volume Pricing
Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Dimensions (mm):
50.0 x 50.0

Angle of Incidence (°):
45.00

Cut-On Wavelength (nm):
615.00

Substrate: N-BK7
Length (mm): 50.00
Coating: Traditional Coated
Color: Red
Reflection (%): R_{abs} = 50% @ 615nm R_{avg} > 98% @ 640-750nm
Reflection Wavelength (nm): 640 - 750
Surface Quality: 60-40
Thickness (mm): 4.00
Thickness Tolerance (mm): ±0.20
Transmission (%): 90.00
Transmission Wavelength (nm): 400 - 595
Type: Dichroic Filter
Width (mm): 50.00
Wavelength Tolerance (nm): ±15
Parallelism (arcmin): <1
Dimensional Tolerance (mm): ±0.25
Clear Aperture (%): 90.00
Coating Specification: Surface 1: Multi-Layer Dichroic Surface 2: Single Layer MgF₂
Wavelength Range (nm): 400 - 750
Surface Flatness (P-V): λ/4

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant