

In order to provide more accurate inventory information, please select your shipping country.

Select Your Country/Region: European Union



SUBMIT

TECHSPEC® 50R/50T VIS, C-Mounted Plate Beamsplitter



Stock #49-685 3-4 DAYS



1



€295,00

ADD TO CART

Qty 1-4

€295,00

Qty 5+

€259,00

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Coating Specification:
Surface 2: Multi-Layer Anti-Reflection for Visible Region

Construction:
Plate

Dimensional Tolerance (mm):
+0.0/-0.25

Extension Length (mm): 38.0
Housing: Black Anodized Aluminum
Housing Dimension: 38 x 38 x 50
Mount: C-Mount Enclosure
Reflection/Transmission Ratio (R/T): 50/50
Reflection/Transmission Tolerance (%): ±5
Substrate: ☐ N-BK7
Surface Flatness (P-V): 1λ
Surface Quality: 60-40
Thread Type: C-Mount (1" x 32 TPI)
Type: Standard Beamsplitter
Wavelength Range (nm): 400 - 700
Beamsplitter Included: #49-754

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant
