

51 x 76mm, 50R/50T, Plate Beamsplitter



Stock #31-433 3-4 DAYS

⊖ 1 ⊕ **€81,00**

ADD TO CART

Qty 1-9
€81,00
Qty 10+
€60,00
Volume Pricing
Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Coating Specification:
Surface 1: Dielectric, ±5% R/T @ 550nm
Surface 2: Uncoated

Construction:
Plate

Dimensional Tolerance (mm):
±0.38

Dimensions (mm): 51.0 x 76.0
Edges: Cut
Reflection/Transmission Ratio (R/T): 50/50
Substrate: ☐ Float Glass
Surface Flatness (P-V): 4 - 6λ
Surface Quality: 80-50
Thickness (mm): 3.00
Type: Standard Beamsplitter
Wavelength Range (nm): 400 - 700

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant