

In order to provide more accurate inventory information, please select your shipping country:

Select Your Country/Region: European Union

SUBMIT

532nm CWL, 25.4mm Dia., OD 6 Ultra Narrow Filter



Ultra Narrow Bandpass Filters



Stock #36-640 3-4 DAYS

- 1 +

€1.492,00

ADD TO CART

Qty 1-9

€1.492,00

Qty 10+

€1.350,00

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Diameter (mm):
25.40

Angle of Incidence (°):

0
Optical Density OD (Average): 6.00
Clear Aperture CA (mm): 21.30
Center Wavelength CWL (nm): 532.00
Full Width-Half Max FWHM (nm): 1.20
Substrate:  BOROFLOAT®
Minimum Transmission (%): >95
Coating: Hard Coated
Transmission (%): T _{abs} >95% @ 532nm (nominal)
Type: Bandpass Filter
Blocking Wavelength Range (nm): 200 - 520, 544 - 1200
Construction: Mounted in Black Anodized Ring
Mount Thickness (mm): 5.0
Note: Filter Design: Multi-Cavity
Substrate Thickness (mm): 2.00

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 240: Compliant