


In order to provide more accurate inventory information, please select your shipping country.

Select Your Country/Region: European Union

SUBMIT



OD 2.0 Shortpass Filters

Stock #15-258 3-4 DAYS



1



€104,00

ADD TO CART

Qty 1-9

€104,00

Qty 10+

€93,60

Volume Pricing

[Request Quote](#)

⚠ Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Diameter (mm):
25.00 +0.00/-0.20

Angle of Incidence (°):
0

Optical Density OD (Average):
≥2.0

Cut-Off Wavelength (nm): 550.00 ±11
Substrate: 
Coating: Hard Coated
Rejection Wavelength (nm): 575 - 710
Surface Quality: 60-40
Thickness (mm): 2.00 ±0.10
Transmission (%): ≥85
Transmission Wavelength (nm): 375 - 530
Type: Shortpass Filter
Clear Aperture (%): 90
Environmental Durability: ML-STD-810F, Section 507.4
Physical Durability: ML-C-48497A, Section 3.4.1
Wavelength Range (nm): 375 - 710

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View