


550nm, 6 x 6mm, OD 2.0 Longpass Filter



OD 2.0 Longpass Filters

Stock #15-201 3-4 DAYS

⊖ 1 ⊕ **€45,00**

ADD TO CART

Qty 1-9
€45,00

Qty 10+
€40,50

Volume Pricing
Request Quote

⚠ Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Dimensions (mm):
6.00 x 6.00 +0.00/-0.20

Angle of Incidence (°):
0

Optical Density OD (Average):
≥2.0

Cut-On Wavelength (nm): 550.00 ±11
Substrate: 
Length (mm): 6.00
Coating: Hard Coated
Rejection Wavelength (nm): 400 - 525
Surface Quality: 60-40
Thickness (mm): 2.00 ±0.10
Transmission (%): ≥85
Transmission Wavelength (nm): 575 - 1600
Type: Longpass Filter
Width (mm): 6.00
Clear Aperture (%): 90
Environmental Durability: ML-STD-810F, Section 507.4
Physical Durability: ML-C-48497A, Section 3.4.1
Wavelength Range (nm): 400 - 1600

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View