

In order to provide more accurate inventory information, please select your shipping country:

Select Your Country/Region: European Union



SUBMIT

5.90" X 5.90" , 1.18" Focal Length, Fresnel Lens



Aspherically Contoured Fresnel Lenses

Stock #13-459 3-4 DAYS



1



€103,00

ADD TO CART

Qty 1-10

€103,00

Qty 11+

€91,50

Volume Pricing

[Request Quote](#)

⚠ Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Effective Focal Length EFL (mm):
30.00

Substrate: ☐
Acrylic

Coating:
Uncoated

Type: Fresnel Lens
Wavelength Range (nm): 400 - 1100
Center Thickness CT (inches): 0.08
Dimensional Tolerance (inches): ±0.05
Dimensions (inches): 5.9 x 5.9
Dimensions (mm): 150.0 x 150.0
Effective Focal Length EFL (inches): 1.18
Groove Density (grooves/inch): 125
Index of Refraction n_d: 1.49
Operating Temperature (°C): 80 (Maximum)
Thickness Tolerance (%): ±40
Transmission (%): 85 (Typical)

Regulatory Compliance

RoHS 2015: Compliant
Reach 219: Compliant
Certificate of Conformance: View