

In order to provide more accurate inventory information, please select your shipping country.

Select Your Country/Region: European Union



SUBMIT



Stock #19-538 3-4 DAYS



1



€238,00

ADD TO CART

Qty 1-9

€238,00

Qty 10+

€212,50

Volume Pricing

Get Product Downloads



Output Power (mW):
5

Wavelength (nm):
635.00

Weight (g):
162

Power Requirement:
1 AA Battery (Not Included)

Style:
Gaussian Line

Output Type:
Free Space

Laser Class - CDRH:
1M

Color:
Red

Fan Angle (°):
90.00

Focus Range:
Up to 1,200mm

Length (mm):
124.00

Environmental Rating:
IP40

Regulatory Compliance

RoHS:
[Compliant](#)

Certificate of Conformance:
[View](#)