

In order to provide more accurate inventory information, please select your shipping country:

Select Your Country/Region: European Union



SUBMIT

TECHSPEC® 5mm 1064nm, Laser Line λ /20 High Tolerance Right Angle Mirror



Stock #37-658 3-4 DAYS



1



€211,00

ADD TO CART

Qty 1-5

€211,00

Qty 6+

€169,00

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Surface Flatness (P-V):
 λ /20

Substrate: ☐
[Fused Silica](#) (Corning 7980)

Surface Quality:
20-10

Length of Legs (mm): 5.00
Dimensional Tolerance (mm): +0.00/-0.10
Coating Specification: R _{abs} >99.8% @ 1064nm @ 45° AOI R _{avg} >99.5% @ 1046 - 1074nm @ 45° AOI
Coating: Laser Mirror (1064nm)
Bevel: Protective bevel as needed
Clear Aperture (%): 90
Design Wavelength DWL (nm): 1064
Length of Hypotenuse (mm): 7.10
Type: Right Angle Mirror
Pyramid Tolerance (arcmin): ±1
Angle Tolerance (arcsec): ±15
Damage Threshold, Reference: ☐ 1MW/cm² @ 1064nm

Regulatory Compliance

RoHS 2015: Compliant
Reach 209: Compliant
Certificate of Conformance: View