

In order to provide more accurate inventory information, please select your shipping country.

Select Your Country/Region: European Union



SUBMIT



N-BK7 Right Angle Prisms

Stock #32-329 ☐ In Stock



1



€57,00

ADD TO CART

Qty 1-5

€57,00

Qty 6+

€51,30

Volume Pricing

[Request Quote](#)

⚠ Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Coating:

Aluminum with protective overcoat

Substrate: ☐

[N-BK7](#)

Surface Quality:

60-40

Type: Right Angle Prism
Dimensional Tolerance (mm): ±0.1
Angle Tolerance (arcmin): ±2
Bevel: Protective bevel as needed
Length of Hypotenuse (mm): 7.10
Length of Legs (mm): 5.00
Image Orientation: Left-Handed
Coating Specification: Reflective Surfaces: R _{avg} >85% FROM 400-700nm, @ 45° AOI
Ray Deviation (°): 90
Wavelength Range (nm): 400 - 700
Damage Threshold, By Design: ☐ Hypotenuse: 0.3 J/cm ² @ 532nm & 1064nm, 10ns
Power (fringes) @ 632.8nm: 1.25
Irregularity (fringes) @ 632.8nm: 0.50

Regulatory Compliance

RoHS 2015: Compliant
Reach 219: Compliant
Certificate of Conformance: View