

In order to provide more accurate inventory information, please select your shipping country.

Select Your Country/Region: European Union

SUBMIT

5mm FL Ultra High Resolution Fixed Focal Length Lenses



#68-681

Stock #68-681 3-4 DAYS



1



€1.875,00

ADD TO CART

Qty 1+

€1.875,00

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Field of View @ Min Working Distance (mm):
142.5

Iris Option:
Variable

Length (mm):
57.10

Horizontal Field of View, 1/2" Sensor:
142.5mm - 64.9°

Filter Thread:

M46 x0.75
Maximum Diameter (mm): 48.0
Weight (g): 120.00
Maximum Image Circle (mm): 11.00
Type: Fixed Focal Length Lens
Focal Length FL (mm): 5.00
Maximum Sensor Format: 2/3"
Working Distance (mm): 100 - ∞
Mount: C-Mount
Aperture (f/#): f/1.8 - f/16
Maximum Distortion (%): <-0.33%
Lens Wavelength Range: VIS

Regulatory Compliance

RoHS 2015: Exempt
Certificate of Conformance: View
Reach 240: Contains SVHC(s)