

In order to provide more accurate inventory information, please select your shipping country.

Select Your Country/Region: European Union



SUBMIT



TECHSPEC Nd:YAG Laser Line λ /20 UV Fused Silica Right Angle Prisms

Stock #37-622 3-4 DAYS



1



€288,00

ADD TO CART

Qty 1-5

€288,00

Qty 6+

€230,50

Volume Pricing

[Request Quote](#)

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Angle Tolerance (arcsec):
±15

Coating:
Laser V-Coat (355nm)

Design Wavelength DWL (nm):
355

Substrate: Fused Silica (Corning 7980)
Surface Quality: 20-10
Type: Right Angle Prism
Dimensional Tolerance (mm): +0.00/-0.10
Bevel: Protective bevel as needed
Clear Aperture (%): 90
Length of Hypotenuse (mm): 7.10
Length of Legs (mm): 5.00
Pyramid Tolerance (arcmin): ±1
Image Orientation: Left-Handed
Coating Specification: R_{abs} <0.25% @ 355nm
Surface Flatness (P-V): λ/20
Damage Threshold, By Design: ☐ 7.5 J/cm², 20ns, 20 Hz

Regulatory Compliance

RoHS 2015: Compliant
Reach 209: Compliant
Certificate of Conformance: View