


TECHSPEC® 5mm Protected Gold Coated, N-BK7 Right Angle Mirror



Stock **#47-027** [CONTACT US](#)

- 1 + **€105,00**

ADD TO CART

Qty 1-5
€105,00

Qty 6+
€84,00

Volume Pricing
Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Surface Flatness (P-V):
λ/8

Substrate:
[N-BK7](#)

Surface Quality:
20-10

Length of Legs (mm): 5.00
Dimensional Tolerance (mm): ±0.1
Coating Specification: R_{avg} >96% @ 700 - 2000nm R_{avg} >96% @ 2000 - 10,000nm
Coating: Protected Gold (700-10000nm)
Coating Type: Metal
Angle Tolerance (arcmin): ±2
Bevel: Protective bevel as needed
Clear Aperture CA (mm): 6.36 x 4.50
Length of Hypotenuse (mm): 7.10
Type: Right Angle Mirror
Wavelength Range (µm): 0.7 - 10
Wavelength Range (nm): 700 - 10000
Damage Threshold, Reference: ☐ 0.8 J/cm² @ 1064nm, 10ns

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant