

In order to provide more accurate inventory information, please select your shipping country:

Select Your Country/Region: European Union

SUBMIT

TECHSPEC® 5mm VIS, Polarizing Cube Beam splitter



TECHSPEC® Broadband Polarizing Cube Beam splitters

Stock #48-998 3-4 DAYS



1



€316,00

ADD TO CART

Qty 1-5

€316,00

Qty 6+

€253,00

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Beam Deviation (arcmin):
±3

Clear Aperture (%):
90

Coating Specification:
R_{avg} <0.5% @ 420 - 680nm

Construction: Cube
Dimensions (mm): 5.0 x 5.0 x 5.0 ±0.1
Extinction Ratio: 500:1
P-Polarization Transmission (%): >90
S-Polarization Reflection (%): >99
Substrate:  N-SF11
Surface Flatness (P-V): λ/8
Surface Quality: 40-20
Type: Linear Polarizer
Wavelength Range (nm): 420 - 680

Regulatory Compliance

RoHS 2015: Compliant
Reach 219: Compliant
Certificate of Conformance: View