

In order to provide more accurate inventory information, please select your shipping country.

Select Your Country/Region: European Union



SUBMIT

5mW Linear Polarization, Lasos Hene Laser



Stock #35-210 ☐ In Stock



1



€782,00

ADD TO CART

Qty 1+

€782,00

Volume Pricing

[Request Quote](#)

 Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Output Power (mW):
5

Polarization:
≥500:1

Wavelength (nm):
632.80

Weight (g):
650.00

Laser Class - IEC:
3B

Power Supply: Power Supply Required and Sold Separately. USA: #35-219 Europe: #35-219 Japan: Not Available Korea: Not Available China: Not Available
Static Alignment: Centered to Outer Cylinder: ≤0.5mm Parallel to Outer Cylinder: ≤1.25
Pointing Stability (mrad/°C): ≤0.1
RMS Noise: 30Hz–10MHz ≤1%
Beam Diameter (mm): 0.8
Type of Laser: HeNe
Beam Divergence (mrad): ≤1.1
Laser Class - CDRH: IIIb
Length (mm): 400.00
Longitudinal Mode Spacing, Nominal (MHz): 438.00
Diameter of Laser Head (mm): 45
Length of Laser Head (mm): 400

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View