

5X EO M Plan Apo Long Working Distance Infinity Corrected



50XEOMPlan Apo Long Working Distance Infinity Corrected, #59-879

Stock **#59-876** 3-4 DAYS



1



€715,00

ADD TO CART

Qty 1+

€715,00

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Field of View (mm):
4.80

Horizontal Field of View, 1/2" Sensor:
1.28mm

Horizontal Field of View, 2/3" Sensor:
1.76mm

Horizontal Field of View, 1" Sensor:
2.56mm

Focal Length FL (mm):

40.00
Length (mm): 61.00
Length excluding Threads (mm): 61.00
Magnification: 5X
Maximum Diameter (mm): 34
Numerical Aperture NA: 0.14
Mounting Threads: M26 x36 TPI
Compatible Tube Lens Focal Length (mm): Focal Length: 200mm
Type: Microscope Objective
Resolving Power (µm): 2.0
Depth of Field (µm): 14.00
Field of View, 24 Diameter Field Eyepiece (mm): 4.8
Operating Temperature (°C): +10 to +40
Operating Humidity: <85% with no condensation
Working Distance (mm): 34.0
Weight (g): 260
Wavelength Range (nm): 390 - 780
Style: Infinity Corrected
Field Number (mm): 24
Parfocal Length (mm): 95
Immersion Liquid: N/A

Regulatory Compliance

RoHS: Exempt
Certificate of Conformance: View