


6 x 6 x 0.5mm, 1030nm SHG, Type I BBO Nonlinear Crystal



Mounted Type I BBO Nonlinear Crystal

Stock #11-169 3-4 DAYS



1



€595,00

ADD TO CART

Qty 1-2

€595,00

Qty 3+

€525,00

Volume Pricing

[Request Quote](#)

⚠ Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Crystal Type:
BBO

Design Wavelength DWL (nm):
1030

Clear Aperture CA (mm):
5.70

Dimensions (mm): 6.0 x6.0 +0.0/-0.1
Thickness (mm): 0.50 +0.0/-0.1
Protective Chamfer: <0.1mm x45°
Orientation Θ/φ (°): 23.4/90
Coating: AR Coating
Coating Specification: S1: 515 & 1030nm Protective Coating S2: 515 & 1030nm Protective Coating
Parallelism (arcsec): <20
Perpendicularity (arcmin): <5
Surface Quality: 20-10
Surface Flatness (P-V): λ/8
Mount: Mounted
Mount Diameter (mm): 25.4
Mount Thickness (mm): 6 (unthreaded)
Typical Applications: SHG @ 1030nm, Type I
Type: Nonlinear Crystal
Damage Threshold, By Design: ☐ 10 J/cm ² @ 1064nm, 10ns, 10Hz
Note: Mount is 25.4mm Dia., 6mm Thick Unthreaded Black Anodized Metal Mount (see drawing for more information)

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant