

Richardson Gratings™ 600 Grooves, 12.5 x 25mm, 500nm, Plane Ruled Reflection Grating

See More by [Richardson Gratings™](#)



Richardson Gratings™ High Precision Plane Ruled Reflective Diffraction Gratings



Stock **#15-765** 3-4 DAYS



1



€152,00

ADD TO CART

Qty 1+

€152,00

Volume Pricing

[Request Quote](#)

⚠ Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Groove Density (grooves/mm):
600

Wavelength Range (nm):
350 - 800

Blaze Wavelength (nm):

500 ±25
Blaze Angle (°): 8.6
Peak Efficiency, Typical (%): 69
Dimensions (mm): 12.5 x 25.0 ±0.1
Clear Aperture (%): >90
Coating: Aluminium
Construction: Ruled Grating
Length (mm): 25.00
Substrate: ☐ Float Glass
Thickness (mm): 6.00 ±0.5
Type: Reflective Diffraction Grating
Width (mm): 12.50
Reflected Wavefront, RMS: $\lambda/4$
Centering of Ruled Area on Substrate (mm): ±1
Alignment of Grooves to Edge (°): ±0.15
Groove Spacing Tolerance (%): <0.05
Polarization: S, P and Average
Master Reference: 1670
Spectral Order (m): 1

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View