

600 Grooves, 25mm Square, 300nm Ruled Diffraction Grating



Reflective Ruled Diffraction Gratings

Stock #43-001 3-4 DAYS



1



€134,00

ADD TO CART

Qty 1+

€134,00

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Groove Density (grooves/mm):
600

Blaze Wavelength (nm):
300

Blaze Angle (°):
5.15

Dimensions (mm):
25.0 x 25.0 ±0.5

Clear Aperture (%) : 90
Coating: Bare Aluminum
Construction: Ruled Grating
Direction of Grooves: Parallel to Short Dimension
Length (mm): 25.00
Substrate: ☐ Float Glass
Thickness (mm): 9.50 ±0.5
Type: Reflective Diffraction Grating
Width (mm): 25.00
Alignment of Grooves to Edge (°): ±0.5
Absolute Peak Efficiency, Typical (%) : 74
Peak Efficiency Avg, Typical (%) : >70

Regulatory Compliance

RoHS 2015: Compliant
Reach 219: Compliant
Certificate of Conformance: View
