

60X Nikon Achromatic Finite Conjugate Objective

See More by [Nikon](#)



60X Nikon Achromatic Finite Conjugate Objective

Stock #59-937 3-4 DAYS

⊖ 1 ⊕ **€192,00**

ADD TO CART

Qty 1+

€192,00

Volume Pricing

[Request Quote](#)

! Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Compatible Cover Glass Thickness (mm):
0.17

Effective Focal Length EFL (mm):
2.87

Field of View (mm):
0.30

Model Number:
MSB50600

Magnification:
60X

Maximum Sensor Format:
2/3"

Numerical Aperture NA:
0.80

Mounting Threads:
RMS / 20.32mm x 36 TPI

Type:
Achromatic, Spring Loaded Head

Resolving Power (μm):
0.3

Depth of Field (μm):
0.30

Working Distance (mm):
0.24

Style:
Finite Conjugate

Manufacturer:
Nikon

Field Number (mm):
18

Immersion Liquid:
N/A

Regulatory Compliance

RoHS:
[Compliant](#)

Certificate of Conformance:
[View](#)
