

In order to provide more accurate inventory information, please select your shipping country.

Select Your Country/Region: European Union

SUBMIT

TECHSPEC® 6.25mm Dia X -12.5mm FL MgF₂ Coated, Illumination Grade PCV Cylinder Lens



TECHSPEC® Illumination Grade PCV Cylinder Lenses

Stock #48-372 3-4 DAYS

1 €70,50

ADD TO CART

Qty 1-5

€70,50

Qty 6+

€56,50

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Diameter (mm):
6.25 +0.0/-0.2

Effective Focal Length EFL (mm):
-12.50

Substrate: ☐
[N-BK7](#)

f/#: 2.00
Numerical Aperture NA: 0.25
Coating: MgF ₂ (400-700nm)
Type: Cylinder Lens, Plano-Concave
Wavelength Range (nm): 400 - 700
Back Focal Length BFL (mm): -13.16
Center Thickness CT (mm): 1.00
Center Thickness Tolerance (mm): ±0.1
Coating Specification: R _{avg} ≤1.75% @400 - 700nm
Edge Thickness ET (mm): 1.80
Focal Length Tolerance (%): ±3
Radius R₁ (mm): -6.48
Surface Quality: 60-40
Damage Threshold, By Design: ☐ 10 J/cm ² @ 532nm, 10ns

Regulatory Compliance

RoHS 2015: Compliant
Reach 209: Compliant
Certificate of Conformance: View