

TECHSPEC® 6.25mm Dia x -6.25mm FL Uncoated, Illumination Grade PCV Cylinder Lens



TECHSPEC® Illumination Grade PCV Cylinder Lenses

Stock **#46-191** 3-4 DAYS

⊖ 1 ⊕ **€59,50**

ADD TO CART

Qty 1-5

€59,50

Qty 6+

€47,50

Volume Pricing

[Request Quote](#)

⚠ Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Diameter (mm):
6.25 +0.0/-0.2

Effective Focal Length EFL (mm):
-6.25

Substrate: □
[N-BK7](#)

f/#: 1.00
Numerical Aperture NA: 0.50
Coating: Uncoated
Type: Cylinder Lens, Plano-Concave
Wavelength Range (nm): 350 - 2200
Back Focal Length BFL (mm): -6.91
Center Thickness CT (mm): 1.00
Center Thickness Tolerance (mm): ±0.1
Edge Thickness ET (mm): 3.38
Focal Length Tolerance (%): ±3
Radius R₁ (mm): -3.24
Surface Quality: 60-40

Regulatory Compliance

RoHS 2015: Compliant
Reach 224: Compliant
Certificate of Conformance: View