

633nm, λ/4 Polymer Waveplate



Polymer Waveplates (Retarders)

Stock #90-941 3-4 DAYS



1



€431,00

ADD TO CART

Qty 1-5

€431,00

Qty 6+

€345,00

Volume Pricing

[Request Quote](#)

⚠ Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Coating:
R_{avg} <0.5% @ 400 - 700nm

Design Wavelength DWL (nm):
633

Diameter (mm):
25.00

Substrate: B270
Retardance: λ/4
Thickness (mm): 2.00
Thickness Tolerance (mm): ±0.2
Type: Polymer Waveplate
Parallelism (arcmin): 3.00
Dimensional Tolerance (mm): +0.0/-0.2
Construction: Birefringent Polymer Stack
Retardance Tolerance (nm): ±10 @ 633
Retardance Order: 0

Regulatory Compliance

RoHS 2015: Compliant
Reach 224: Compliant
Certificate of Conformance: View
