

63.5mm Clear Aperture, 2 Arcsec, Aluminum Retroreflector



Stock #46-177 3-4 DAYS

- 1 + **€1.430,00**

ADD TO CART

Qty 1+
€1.430,00

Volume Pricing
Request Quote

Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Beam Deviation (arcsec): 2.00
Clear Aperture CA (mm): 63.5
Coating: Enhanced Aluminum (450-650nm)
Diameter (mm): 89.40
Exiting Wavefront Accuracy: 0.6λ

Substrate: 
Surface Quality: 80-50
Mounting Threads: (6) ¼-20, (5) M6 x 1.0
Type: Retroreflector
Dimensional Tolerance (mm): ±1.6
Image Orientation: Left-Handed
Ray Deviation (°): 180
Wavelength Range (nm): 400 - 700

Regulatory Compliance

RoHS 2015: Compliant
REACH 201: Compliant
Certificate of Conformance: View