

TECHSPEC® 6.35mm Dia. x 25.4mm EFL, Protected Gold 50Å 90° Off-Axis Mirror



TECHSPEC Gold Off-Axis Parabolic Mirrors

Stock **#37-296** 3-4 DAYS

[Other Coating Options](#)

⊖ 1 ⊕ **€220,00**

ADD TO CART

Qty 1-5

€220,00

Qty 6+

€198,00

Volume Pricing

[Request Quote](#)

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Type:
Off-Axis Parabolic Mirror

Diameter (mm):
6.35 +0.1/-0.0

Effective Focal Length EFL (mm): 25.40
Focal Length Tolerance (%): ±1
Radius of Curvature (mm): 25.40
Coating: Protected Gold (700-10000nm)
Coating Type: Metal
Coating Specification: R _{avg} ≥94% @ 700 - 800nm R _{avg} ≥97% @ 800 - 2,000nm R _{avg} ≥98% @ 2,000 - 12,000nm
Off-Set Angle (°): 90
Parent Focal Length PFL (mm): 12.7
Surface Figure, RMS: λ/8
Surface Roughness (Angstroms): <50 RMS
Wavelength Range (nm): 700 - 10000
Surface Quality: 80-50
Compatible Mounting Plates: #37-943
Substrate: Aluminum 6061-T6
Y Offset (mm): 25.40
Reflected Wavefront, RMS: λ/4

Regulatory Compliance

RoHS 2015: Compliant
Reach 209: Compliant
Certificate of Conformance: View
