

In order to provide more accurate inventory information, please select your shipping country.

Select Your Country/Region: European Union



SUBMIT



Stock #17-160 [CONTACT US](#)



1



€74,00

ADD TO CART

Qty 1-49

€74,00

Qty 50+

€57,00

Volume Pricing

[Request Quote](#)

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Length (mm):
29.60

Maximum Diameter (mm):
19

Maximum Image Circle (mm):
8.00

Note:

High Resolution
Type: M12 Imaging Lens
Focal Length FL (mm): 6.96
Maximum Sensor Format: 1/2"
Working Distance (mm): 400 - ∞
Mount: M12 x0.5 (S-Mbunt)
Aperture (f/#): f/1.6
IR Cut Filter: No
Lens Wavelength Range: VIS

Regulatory Compliance

Certificate of Conformance: View
--