

In order to provide more accurate inventory information, please select your shipping country.

Select Your Country/Region: European Union



SUBMIT

TECHSPEC® 6mm Dia X 18mm FL Uncoated, Illumination Grade PCX Cylinder Lens



Stock #68-027 3-4 DAYS

1 €59,50

ADD TO CART

Qty 1-5

€59,50

Qty 6+

€47,50

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Diameter (mm):
6.00

Effective Focal Length EFL (mm):
18.00

Substrate: ☐
N-BK7

f/#: 3
Numerical Aperture NA: 0.17
Coating: Uncoated
Type: Cylinder Lens, Plano-Convex
Wavelength Range (nm): 350 - 2200
Back Focal Length BFL (mm): 16.81
Center Thickness CT (mm): 1.80
Center Thickness Tolerance (mm): ±0.1
Dimensional Tolerance (mm): +0.0/-0.2
Edge Thickness ET (mm): 1.30
Focal Length Tolerance (%): ±3
Radius R₁ (mm): 9.30
Surface Quality: 60-40

Regulatory Compliance

RoHS 2015: Compliant
REACH 201: Compliant
Certificate of Conformance: View