

# 6" Red Advanced Illumination High Intensity Ring Light

See More by [Advanced Illumination](#)



Stock **#88-492** 3-4 DAYS

- 1 +

€1.323,00

ADD TO CART

|           |
|-----------|
| Qty 1+    |
| €1.323,00 |

|                               |
|-------------------------------|
| Volume Pricing                |
| <a href="#">Request Quote</a> |

ⓘ Prices shown are exclusive of VAT/local taxes

**Note:** This item requires accessories for use | [Learn More](#)

|                       |
|-----------------------|
| Get Product Downloads |
|-----------------------|

Color:  
Red

Diameter (mm):  
152.40

Height (mm):

|                                                                                                                                                                                                                                             |
|---------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| 26.7                                                                                                                                                                                                                                        |
| <b>Inner Diameter (mm):</b><br>66.00                                                                                                                                                                                                        |
| <b>Model Number:</b><br>RL 113-625-IC                                                                                                                                                                                                       |
| <b>Operating Temperature (°C):</b><br>0 to 60                                                                                                                                                                                               |
| <b>Outer Diameter (mm):</b><br>152.4                                                                                                                                                                                                        |
| <b>Wavelength (nm):</b><br>625.00                                                                                                                                                                                                           |
| <b>Weight (g):</b><br>681.00                                                                                                                                                                                                                |
| <b>Working Distance (mm):</b><br>225 - 600                                                                                                                                                                                                  |
| <b>LED Lifetime (hours):</b><br>50,000                                                                                                                                                                                                      |
| <b>Power Supply:</b><br>Power Supply Required and Sold Separately.<br>USA: <a href="#">#66-855</a><br>Europe: <a href="#">#66-855</a><br>Japan: <a href="#">#66-855</a><br>Korea: <a href="#">#33-773</a><br>China: <a href="#">#66-855</a> |
| <b>Number of Channels:</b><br>1.00                                                                                                                                                                                                          |
| <b>Type of Illumination:</b><br>LED Illuminator                                                                                                                                                                                             |
| <b>Note:</b><br>Optional Manual Intensity Adjustment <a href="#">#86-887</a> and <a href="#">#89-555</a> are Available                                                                                                                      |
| <b>Manufacturer:</b><br>Advanced Illumination                                                                                                                                                                                               |
| <b>Geometry:</b><br>Ring Light                                                                                                                                                                                                              |
| <b>Illumination Mode:</b><br>Constant                                                                                                                                                                                                       |
| <b>Environmental Rating:</b><br>IP67                                                                                                                                                                                                        |

Regulatory Compliance

|                                                            |
|------------------------------------------------------------|
| <b>RoHS 2015:</b><br><a href="#">Compliant</a>             |
| <b>Certificate of Conformance:</b><br><a href="#">View</a> |
| <b>Reach 233:</b><br><a href="#">Contains SVHC(s)</a>      |