

In order to provide more accurate inventory information, please select your shipping country.

Select Your Country/Region: European Union



SUBMIT

TECHSPEC® 70mm, Side Drive, Standard Top, Metric Micrometer Stage



70mm, Side Drive, Solid Top, Micrometer Stage

Stock #66-436 [CONTACT US](#)



1



€435,00

ADD TO CART

Qty 1-2

€435,00

Qty 3+

€379,60

Volume Pricing

[Request Quote](#)

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Type of Movement:
Linear (X)

Guide System:
Crossed Roller Bearing

Type of Drive:
Metric Micrometer

Drive Orientation: Side Drive
Type: Metric
Stage Size (mm): 70 x 70
Travel (mm): 13
Center Hole: M6 x 1
Construction: Aluminium Stage
Leadscrew Pitch (mm): 0.5
Load Capacity (kg): 8
Mounting Threads: (8) M6 x 1, (4) M3 x 0.5, (8) M2 x 0.4
Stage Size (inches): 2.75 x 2.75
Straight Line Accuracy (µm): 2
Pitch (arcsec): 30
Yaw (arcsec): 25

Regulatory Compliance

RoHS 2015: Exempt
Certificate of Conformance: View
Reach 233: Contains SVHC(s)
