

TECHSPEC® 70R/30T 30mm Dia., UV Plate Beamsplitter



TECHSPEC® UV Plate Beamsplitters

Stock **#84-489** 3-4 DAYS



1



€152,00

ADD TO CART

Qty 1-5

€152,00

Qty 6+

€121,50

Volume Pricing

[Request Quote](#)

⚠ Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Angle of Incidence (°):

45

Clear Aperture (%):

>85

Coating Specification:

Surface 1: R_{abs} = 70 ±5% @ 350nm, R_{avg} = 70 ±10%

over 250 - 450nm T _{abs} =30 ±5% @ 350nm, T _{avg} = 30 ±10% over 250 - 450nm Surface 2: BBAR (R _{avg} <1%, R _{abs} <2% over 250 - 450nm)
Construction: Plate
Diameter (mm): 30.00
Dimensional Tolerance (mm): +0.0/-0.2
Parallelism (arcmin): <5
Reflection/Transmission Ratio (R/T): 70/30
Substrate:  Fused Silica (Corning 7980)
Surface Flatness (P-V): 1λ
Surface Quality: 60-40
Thickness (mm): 3.00
Thickness Tolerance (mm): ±0.38
Type: Standard Beamsplitter
Wavelength Range (nm): 250 - 450

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant