

In order to provide more accurate inventory information, please select your shipping country.

Select Your Country/Region: European Union



SUBMIT

TECHSPEC® 75 X 75mm Protected Silver, $\lambda/4$ Mirror



Stock #88-541 [CONTACT US](#)

- 1 + €235,00

ADD TO CART

Qty 1-5

€235,00

Qty 6+

€188,00

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Surface Flatness (P-V):
 $\lambda/4$

Substrate: BOROFLOAT®

Back Surface:
Commercial Polish

Surface Quality: 60-40
Dimensions (mm): 75.0 x 75.0
Dimensional Tolerance (mm): ±0.25
Coating Specification: R _{avg} >98% @450 - 2000nm R _{avg} >98% @2000 - 10,000nm
Coating: Protected Silver (450-10000nm)
Coating Type: Metal
Bevel: Protective bevel as needed
Clear Aperture (%) : 85
Edges: Fine Ground
Thickness (mm): 12.00 ±0.25
Type: Flat Mirror
Wavelength Range (µm): 0.45 - 10
Wavelength Range (nm): 450 - 10000
Length (mm): 75.00
Width (mm): 75.00
Damage Threshold, Reference:  0.5 J/cm ² @532nm & 1064nm, 10ns

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant