

76.2mm Dia., Gold Coated, Aluminum Substrate Mirror



Stock **#47-120** ☐ In Stock

1 **€651,00**

ADD TO CART

Qty 1-5
€651,00
Qty 6+
€585,90
Volume Pricing
Request Quote

⚠ Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Diameter (mm):
76.20 +0.00/-0.38

Substrate: ☐
Aluminum 6061-T6

Surface Quality:

80-50
Coating Specification: R_{avg} >94% @ 700 - 800nm R_{avg} >97% @ 800 - 2000nm R_{avg} >98% @ 2 - 12μm
Coating: Protected Gold (700-12000nm)
Coating Type: Metal
Clear Aperture (%): 90
Mounting Threads: 8-32 TPI Tapped Holes
Surface Roughness (Angstroms): <175
Thickness (mm): 12.70
Type: Flat Mirror
Wavelength Range (μm): 0.7 - 12
Wavelength Range (nm): 700 - 12000
Surface Flatness (RMS): λ/2

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant